

D

C

B

A



Description: CAT6 molded & booted patch cable
Part No: 73-889X-XXX
Application: Patch cable
Crimp Tool: N/A
Impedance: N/A
Frequency Range: N/A
Material: Plug RJ-45, Gold plated on contacts
Hood PVC
Cable UTP, 24 AWG, 4 twisted pairs with PE divider, stranded bare copper, UL ETL EIA/TIA-568A verified category 6
RoHS Compliance: Yes
Technical Detail: N/A

DRAWING NO.									
73-889X-XXX-CUST									
REVISIONS									
01	OFFICIAL RELEASE								
	06-11-10	J	J	T	H				
02	CHANGE VIEW								
	03-29-11	J	J	D					ECO-11-0058

D

C

B


A

受控 CONTROLLED DOCUMENT					
编号 P/N	73-889X-XXX-CUST	版本 Rev	02	日期 Rel'd Date	Jul11,11

X=COLOR
0-GRAY
1-BLACK
2-BLUE
3-GREEN
4-RED
5-YELLOW
6-WHITE
7-ORANGE
8-PINK
9-PURPLE

TABLE 1

PART NUMBER	LENGTH (FEET)	DESCRIPTION
73-889X-1	1	CAT6 MOLDED & BOOTED PATCH CABLE, 1FT
73-889X-3	3	CAT6 MOLDED & BOOTED PATCH CABLE, 3FT
73-889X-5	5	CAT6 MOLDED & BOOTED PATCH CABLE, 5FT
73-889X-7	7	CAT6 MOLDED & BOOTED PATCH CABLE, 7FT
73-889X-10	10	CAT6 MOLDED & BOOTED PATCH CABLE, 10FT
73-889X-14	14	CAT6 MOLDED & BOOTED PATCH CABLE, 14FT
73-889X-25	25	CAT6 MOLDED & BOOTED PATCH CABLE, 25FT
73-889X-50	50	CAT6 MOLDED & BOOTED PATCH CABLE, 50FT
73-889X-100	100	CAT6 MOLDED & BOOTED PATCH CABLE, 100FT



PIN ASSIGNMENT		
	RJ-45 PLUG	RJ-45 PLUG
WHITE/ORANGE	1	1
ORANGE	2	2
WHITE/GREEN	3	3
GREEN	6	6
BLUE	4	4
WHITE/BLUE	5	5
WHITE/BROWN	7	7
BROWN	8	8

DIM OUTLINE

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE
DECIMALS		JEAN.JIN	03-29-11
X		CHECKED BY	DATE
X.X		JEAN.JIN	03-29-11
X.XX		APPROVED BY	DATE
X.XX		DONALD	03-29-11
ANGLES	± 0.5°	U/M	mm

THIS DRAWING WAS PRODUCED BY COMPUTER.
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

		
TITLE		
CAT6 MOLDED & BOOTED PATCH CABLE		
SHEET	DRAWING NO.	SIZE
1 OF 1	73-889X-XXX-CUST	A

5

4

3

2

1