

HEX NUT AND WASHER
NOT SHOWN
IN VIEW

Ø26.00
[1.024 in]

KC52A30.001NPS
(G510440)

SLOT 11

LOCKING RING
(G200000)

Ø3.00
[.118 in]

5.50
[.217 in] FLAT

3/8-32 UNEF-2A
THREADS

HARDWARE SUPPLIED
ON SWITCH



2.00
[.079 in]

14.20
[.559 in]

8.00
[.315 in]

30.00
[1.181 in]

2.00
[.079 in]



NOTE:

1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
- ▲4. CONTACT MATERIAL: SILVER
5. CONTACT RATING: 150MILLIAMP, 250VAC/DC
350MILLIAMP, 110VAC/DC
6. CONTACT RATING (NON-SWITCHING) 5A
7. OPERATING FORCE 425±100CM/STANDARD
8. OPERATING TEMP: -30°C TO 85°C
- ▲9. CIRCUIT SP: 12 POSITION 30° INDEX.
10. DIELECTRIC STRENGTH: 1000V RMS MIN.@ SEA LEVEL.
- ▲11. HARDWARE SUPPLIED ON SWITCH:
LOCKWASHER, HEXNUT, STOP RING (TAB IN POSITION 11)
12. ▲ DENOTES CRITICAL PARAMETER.
13. 2002/95/EC (ROHS) COMPLIANT



B	17333	FIXED NOTE 9, TOOK OUT NO STOP	5/25/07	TN
A	17189	RELEASED FOR PRODUCTION	4/17/07	TN
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE KC52A30.001NPS W/LOCKRING

SCALE 1.5:1

DATE 5/25/2007

DR TN

DWG XG0005P

REV B