



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		NEW DRAWING	22MAR2017	GK	DB



OUTSIDE WOUND LABEL ACROSS: 2 PER ROLL QTY: 2500

All dimensions in mm [Inch]

UL RECOGNIZED BY UNDERWRITERS LABORATORIES INC. IN UL FILE MH61871-PGIS2 CATEGORY-SBP LABEL, PRINTER AND RIBBON

TE PN: CS4293-000

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED
	0 PLC ±
	1 PLC ±
	2 PLC ±
	3 PLC ±
	4 PLC ±
	ANGLES ±
MATERIAL: SEE TABLE	FINISH: GLOSSY

MATERIAL: LINEAR	CLEAR VINYL
ADHESIVE TYPE	ACRYLIC PERMANENT
	WHITE GLASSINE
DWN: GOPALAKRISHNA HV	TE Connectivity
CHK: D.BURGAT	
APVD: D.BURGAT	
PRODUCT SPEC: TTDS-211	SBP LABEL - WHITE
APPLICATION SPEC:	50.8 x 101.6mm [2.00 x 4.00inch]
SIZE: A2	CAGE CODE: 00779
DRAWING NO: SBP200400WE2.5	RESTRICTED TO: -
WEIGHT: 0.717g	SCALE: NTS
CUSTOMER DRAWING	SHEET: 1 of 1
	REV: A