



## MICRO PUSH-WIRE CONNECTOR FOR JUNCTION BOXES 4-CONDUCTOR TERMINAL BLOCK PUSH-WIRE® CONNECTION




© 1992 - 2011 CADENAS GmbH











## MICRO PUSH-WIRE CONNECTOR FOR JUNCTION BOXES 4-CONDUCTOR TERMINAL BLOCK PUSH-WIRE® CONNECTION 243-144

© 1992 - 2011 CADENAS GmbH

ITEM-NO. (ITEM-NO.)	243-144
DIAMETER1 (DIAMETER / mm)	4 x 0.4 - 0.5
DIAMETER2 (DIAMETER / AWG)	26 - 24
Strip length (Strip length / mm)	5 - 6
Measured voltage (Measured voltage / V)	100
Measured shock voltage (Measured shock voltage / kV)	1.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	6
P (NO. OF POLES)	4
Height (Height / mm)	6.8
Width (Width / mm)	10
Depth (Depth / mm)	10
No. of connection Points (No. of connection Points)	4
No. of potentials (No. of potentials)	1
COLOR (COLOR)	Transparent
WEIGHT (WEIGHT / g)	0.81