



ITEM-NO. (ITEM-NO.)	826-163
Cross section1 (Cross section / mm ²)	0.08 - 4
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	9 - 10
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	32
RM (PIN SPACING / mm)	7
P (NO. OF POLES)	3
Height (Height / mm)	23.55
Width (Width / mm)	22.5
Depth (Depth / mm)	42.5
No. of connection Points (No. of connection Points)	6
No. of potentials (No. of potentials)	3
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	18.5
Comment (Comment)	L = (No. of poles x Pin Spacing) + 1.5 mm