



ITEM-NO. (ITEM-NO.)	806-106
Cross section1 (Cross section / mm ²)	2 x 0.2 - 1.5
Cross section2 (Cross section / AWG)	2 x 24 - 16
Strip length (Strip length / mm)	9 - 10
Measured voltage (Measured voltage / V)	250
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	10
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	6
Height (Height / mm)	16.25
Width (Width / mm)	31.5
Depth (Depth / mm)	19.8
No. of connection Points (No. of connection Points)	12
No. of potentials (No. of potentials)	6
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	7.688
Comment (Comment)	L = (No. of poles x Pin Spacing) + 1,5 mm
Dimensions (Dimensions)	1,3 mm