



C146 D  
für gestanzte Crimpkontakte  
for stamped crimp contacts

Alle technischen Daten wurden unter Laborbedingungen ermittelt und können im Praxisbetrieb abweichen.  
Es handelt sich bei den Angaben weder um Beschaffenheits- noch um Haltbarkeitsgarantien.  
All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding, particularly the information does not constitute or provide any legal guarantees ("Beschaffenheitsgarantie" or "Haltbarkeitsgarantie").

## Characteristics

06	General Characteristics	Standard	Value
number of contacts			40
termination technique			crimp
wire gauge			0,14 mm <sup>2</sup> - 2,5 mm <sup>2</sup> AWG 26 - AWG 14
max. insulation diameter			4,3 mm
flammability	UL 94		V-0
Electrical Characteristics	Standard	Value	
rated voltage	IEC 60664-1		250 V
pollution degree	IEC 60664-1		3
installation (overvoltage) category	IEC 60664-1		3
material group	IEC 60664-1		3a
rated impulse withstand voltage	IEC 60664-1		4 kV
rated current $T_{amb} = 40^{\circ}\text{C}$			10 A
current carrying capacity	IEC 60512-5-2		see derating curve
contact resistance	IEC 60512-2-1		$\leq 5 \text{ m}\Omega$
insulation resistance	IEC 60512-3-1		$\geq 10^{10} \Omega$
Climatical Characteristics	Standard	Value	
climatic category	IEC 60068-1		40 / 125 / 21
upper temperature	IEC 60512-11-9		+125 °C
lower temperature	IEC 60512-11-10		-40 °C
Mechanical Characteristics	Standard	Value	
mechanical operation	IEC 60512-9-1		$\geq 500$ mating cycles
Materials	Standard	Value	
insert			PC GF grey
contacts			CuZn (brass)
contact plating			Ag (silver)/Au (gold)

Gewicht (errechnet) / Calc WT : 55,9 g	Zul. Abw./Tolerances :	DIN / ISO 13715	Maßstab / Scale : 1:1 (1:2)	A3			
Prüfmaß / Testdimension							
Teileindex / Partindexnumber:							
Bagatelle change:							
	Gez. Drawn	11.12.2013 jhoennige					
	Status	Released					
	Gepr. Checked	09.05.2017 MGRIMM					
<b>Amphenol Tuchel Industrial GmbH</b>							
M	C146 10A040 000 2	Blatt/Sheet 1					
Index	Änderung/Description	Datum/Date	Name	NXN-V04 1 Bl.			
Ers. f. / Replacement for : M-C146 10A040 000 2 Rev04							