








THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C	LEN-8B0540	2008/09/22	Shin	Add Note
D	LEN1330121	2013/03/28	Yulong	Change The Dimension
E	LEN1590305	2015/09/02	Vicky	Update Logo



- Note:
- * $\varnothing$ Important Dimension To Check
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF, Black
 - * Male Pin: Copper Alloy, Gold Plated
 - * Nut: Nylon+GF, Black
 - * Gasket: EPDM, Black
 - * Use With Waterproof Cap Or Dust Cap
Panel Thickness Max: 3.0mm
 - * Use Without Waterproof Cap Or Dust Cap
Panel Thickness Max: 4.0mm
- With Liquid Glue

UNIT:mm		
TOLERANCE	.X ±0.25	.XX ±0.1
.XXX ±0.05		
ANGLES	±1°	

TITLE	Standard
Panel Screw 12Pin M Conn M Pin	
SCALE	2:1
SIZE	A4
SHEET	1 OF 1
REV.	E
WC-REV.	B.2
QC	Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	BU-12PMMS-SC7001	DRAWN BY	Vicky	DATE	2015-09-02
DWG NO	BU-12PMMS-SC7001	CHECKED BY	Rita	DATE	2015-09-02
CUSTOMER	ALTW	APPROVED BY	Lion	DATE	2015-09-02