





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8A0143	2008/09/15	Shin	Add Notes
C	LEN1530170	2014/12/18	Ruru	Change Logo



Note:


- * $\varnothing$ Important Dimension.
- * Waterproof Rate: IP67
- * Housing: Black, Nylon+GF
- * Pin: Copper Alloy, Gold Plated
- * Nut: Black, Nylon+GF
- * Gasket: Black, EPDM

$\triangle$ * Use with waterproof cap or dust cap


Panel Thickness max: 2.5mm

$\triangle$ * Use without waterproof cap or dust cap


Panel Thickness max: 3.5mm



Recommended
Panel Cut-Out



Pin Assignments
Front View



UNIT:mm	
TOLERANCE	
.X	±0.25
.XX	±0.1
.XXX	±0.05
ANGLES	±1°

TITLE Mini Panel Lock 4Pin M Conn. M Pin			
SCALE 2:1	SIZE A4	SHEET 1 OF 1	
REV. C	WC-REV. A.1	$\varnothing$: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO. AU-04PMMS-LC7001	DRAWN BY Ruru	DATE 2014-12-18
DWG NO. AU-04PMMS-LC7001	CHECKED BY Rita	DATE 2014-12-18
CUSTOMER ALTW	APPROVED BY Win	DATE 2014-12-18

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.