Alle Rechte vorbehalten/ All rights reserved 47,04 ±0,1 6 -0.3 4-40 UNC-2B Length of engagement: 3,5 D ±0,2 71 38,9 *0,2 Metal frame -O-ring IP67 Ø 0,6 PCB layout, component side, thickness 1,6 mm 23,52 8,28 8 -0,2 5,54 2,84 □ 0,1 (+)62 ±0,2 В Ø1 ±0,1 Ø3 ±0,1 2,84 4,14 Ø 0,1 → | Ø 0,1 000000000 000000000 00000000 6,91 9,68 D-Sub, 17W2, male, straight, Maßstab/ Scale Dat. Name solder pins, rear metal frame, tin plated shell with dimples, 17/04/09 PK Detail. Α Insp. All Dim. in mm guiding pins and board locks, 1,5:1 Orig. Size DIN A 4 O-ring, waterproof IP67 Stand. Blatt/ Page 09 69 390 9014 TB HARTING EURL 09 69 390 9014 0,76 μm Aυ EC00329 17/04/09 PK F-95972 Paris Part number Performance level Mod. Dat. Name

Released / Freigegeben 2009/06/30-07:14:02