



|                |              |
|----------------|--------------|
| 09 67 015 0426 | M3           |
| 09 67 015 0424 | 4-40 UNC     |
| Part number    | Screw thread |

|       |          |      |                               |          |      |  |
|-------|----------|------|-------------------------------|----------|------|--|
|       |          |      |                               | Dot.     | Name |  <p>All Dim. in mm<br/>Orig. Size DIN A 4</p> |
|       |          |      | Detail.                       | 28/03/02 | CV   |  |
|       |          |      | Insp.                         |          |      |  |
|       |          |      | Stand.                        |          |      |  |
| 34784 | 11/02/08 | PK   |                               |          |      |  |
| 31085 | 04/09/02 | CV   | HARTING EURL<br>F-95972 Paris |          |      |   |
| 29760 | 28/03/02 | CV   |                               |          |      |  |
| Mod.  | Dot.     | Name |                               |          |      |  |

|  |                   |
|--|-------------------|
| D-Sub, top entry hood with knurled screws, 15 poles, thermoplastic black | Maßstab/<br>Scale |
|  | 1:1               |
| TB 09 67 015 042X  | Blatt/ Page       |
| Sub.   | 1 / 1             |