



1

2

3

4

5



TECHNICAL CHARACTERISTICS

MATERIAL

INSULATOR: PBT
FLAMABILITY RATING: UL94-V0
MAX. TEMPERATURE: 220°C 10s
COLOR: BLACK
SHIELDING: STEEL TIN PLATED

ENVIRONMENTAL

OPERATING TEMP.: -40°C UP TO 85°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL

CURRENT RATING: 3A MAX
WORKING VOLTAGE: 125V AC
INSULATOR RESISTANCE: >5000 MOHM
DIELECTRIC WITHSTANDING VOLTAGE: 1000V AC/MN

PACKAGING

TRAY

DIMENSION

NB PIN	A	B	C	D	E
9	16.30	25.00	30.80	15.80	19.20
15	24.60	33.30	39.20	24.00	27.70
25	38.30	47.10	53.10	38.00	41.10
37	54.80	63.50	69.40	54.30	57.30

FEMALE CRIMP CONTACT


AWG 20-22 PART NO: 61800213722

AWG 24-26 PART NO: 61800313722

NOTE : NOT COMPATIBLE WITH HOOD 6180xx25311

RoHS Compliant

PROJECTION:



GENERAL TOLERANCE

.X = ± 0.2 .XX = ± 0.15 

APPROVAL: RJ

UNIT: MM

SCALE:

SHEET: 1/1


DRAW: PEARL

DESCRIPTION: D SUB FEMALE TERMINAL HOUSING

WERI PART NO: 618 0xx 217 222

SIZE

A4

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = ± 0.2 .XX = ± 0.15		DESCRIPTION: D SUB FEMALE TERMINAL HOUSING	SIZE A4
J	06-JAN-14	DIM CORRECTION	QL					
I	05-MAR-13	NOTE	QL					
H	22-AUG-12	UL	GG	APPROVAL: RJ	UNIT: MM	SCALE:	WERI PART NO: 618 0xx 217 222	
REV	DATE	FILE	BY					