	1		2		3	4	5	
					4.98	TECHNICAL CHARACTI MATERIAL INSULATOR: PBT FLAMABILITY RATING: COLOR: BLACK WITH F CONTACT MATERIAL: O CONTACT TYPE: STAM CONTACT PLATING: GO QUALITY CLASS: 3 AS I PITCH: 2.54MM	UL94-V0 PULLBACK COPPER ALLOY PED DLD	
		13.75	2.24			ENVIRONMENTAL OPERATING TEMPERA COMPLIANCE: LEAD FF ELECTRICAL CURRENT RATING: 3A WORKING VOLTAGE: 2: INSULATOR RESISTAN DIELECTRIC WITHSTAN CONTACT RESISTANCE PACKAGING BAG	REE AND ROHS 50V AC CE: ≻1000 MOHM NDING VOLTAGE: 500V AC/MN	
		٦		2.54				
D	olds Compliant			PROJECTION:	GENERAL TOLERANCE			
	oHS Compliant				$y = \frac{1}{2} + $			
G F E	29-OCT-12	UL certification	QL		.X = <sup>+</sup> / <sub>-</sub> 0.2 .XX = <sup>+</sup> / <sub>-</sub> 0.15			
G F E D	29-OCT-12 24-NOV-09	STANDARD	JP		.XX = <sup>+</sup> /_ 0.15			
G F E D C	29-OCT-12 24-NOV-09 11-DEC-06	STANDARD DRAW	JP EC	APPROVAL: RJ	.XX = +/_ 0.15 UNIT: MM	WÜRTH ELEKTRONIK DESCRIPTION: 2.54MM JUMPER WITH TEST I	POINT	BIZE
G F	29-OCT-12 24-NOV-09	STANDARD	JP		.XX = <sup>+</sup> /_ 0.15			SIZE <b>A4</b>