





REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2009.04.17	LENGJIANJUN
02	△	變更料號	2008.08.19	彭思城
03	△	修正端子料號	2009.07.25	彭思城
04	△	變更圖號	2011.02.19	黃明霞
05	△	依業務要求增加CAP	2017.06.23	何東華

Specifications  
 Current Rating:1.0Amp  
 Insulation Resistance:1000MΩMin.  
 Dielectric Withstanding Voltage:300VAC  
 Contact Resistance:20mΩMax.  
 Operating Temperature:-40°C to +105°C  
 Materials  
 Contact Material: Brass△  
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 LCP or the equivalent material  
 All materials must meet Greenconn hazardous substances control standards.



Recommended P.C.Board Layout  
 (Tolerance:±0.05)



### Ordering Information △△

G PEA214 - XX XX A 005 C 1 B X

No. of Pins per Row 02~33  
 Standard Plating 02=Gold Flash  
 Selective Plating 01=Tin 05=Gold Flash/Tin  
 Color 1=Black  
 Standard Packing A=Box  
 Selective Packing C=Tube

格菱股份有限公司  
**Greenconn Corporation**

GENERAL TOLERANCE	
X.*±5.0°	X.±0.30
.X*±3.0°	.X±0.25
.XX*±2.0°	.XX±0.15
.XXX*±1.0°	.XXX±0.10

DESIGNED: 何東華	DATE: 2017.06.23
CHECKED:	DATE:
CO SIGNED: 蘭文禮	DATE: 2017.06.23
APPROVED:	DATE:

DWG. NO.	GPEA214-CA5CB
PART NO.	GPEA214-XX XXA005C1BX

TITLE:	1.27 PIN HEADER DUAL ROWS DIP TYPE CONNECTOR
--------	--

REV.	UNIT.	SCALE.	PAGE.
05	mm	5:1	1/1