




Recommended P.C.Board Layout (Tolerance:±0.05)



REV.	LOCAS	DESCRIPTION	DATE	DRAWN
02	△△	新增膠紙配方	27.5.2008	許承佑
03	△△	變更料號	2008.10.06	彭思城
04	△△	變更圖號並修改注解	2011.05.30	黃明霞



Specifications
 Current Rating:1Amp
 Insulation Resistance:1000MΩMin.
 Dielectric Withstanding: 300VAC
 Contact Resistance:20mΩMax.
 Operating Temperature:−40°C to +105°C
Materials
 Contact Material: Brass
 Insulator Material: High Temperature
 Thermoplastic,UL 94V−0 LCP
 or the equivalent material
 All materials must meet Greenconn
 requirement for environment protection.

Ordering Information△

G PED201−XX XX A005 C 1 B X



No. of Pins per Row 02~33
 Standard Plating 02=Gold Flash
 Selective Plating 01=Tin
 05=Gold Flash/Tin
 Standard Packing C=Tube
 Selective Packing D=Tape Reel
 H=acetate tape+T&R

格稜股份有限公司
Greenconn Corporation

GENERAL TOLERANCE	
X.*±5.0°	X.±0.30
.X*±3.0°	.X±0.25
.XX*±2.0°	.XX±0.15
.XXX*±1.0°	.XXX±0.10

DESIGN: 黃明霞	DATE: 2011.05.30
CHECKED: 李新華	DATE: 2011.05.30
AUDITED: LINK	DATE: 2011.05.30

DWG. NO. △△△	GPED201−CA5CB
PART NO. △	GPED201−XXXXA005C1BX

TITLE.
 1.27 PIN HEADER
 DUAL ROWS SMT TYPE
 SIDE ENTRY

REV.	UNIT.	SCALE.	PAGE.
04	mm	1:1	1/1