





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	USE WITH CABLE TIE	HOLE DIAMETER in [mm]	WEIGHT lbs [g] per 100 pcs
HVMPM-08-___	HV , IT	.312 [8.0]	.36 [165.3]
HVMPM32-___			

NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.



ISOMETRIC
1:1

DIMENSIONS IN BRACKETS ARE METRIC [mm]		
CAD FILENAME/LAYERS G00239MB_PB_HVMPM_01		
PANDUIT CORP. TINLEY PARK, ILLINOIS		
HYPER-V MASONRY PUSH MOUNT HVMPM_---		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 [1.3] (.XXX) ±0.010 [0.25] (.XX) ±0.02 [0.5] ANGLES ±5°		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
DRAWN BY TMSA	MAT'L: IMPACT MODIFIED NYLON 6/6 WEATHER RESISTANT BLACK	SCALE 2:1
DATE 02-07-06	CHK'D	DRAWING NO. G00239MB
		DWG A SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
I	10/6/06	JAD		ADD HVMPM32	GB0239MB	I		
R	5-22-06	TMSA		INITIAL RELEASE	GB0239MB	R		