


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT * PART NO.	BUNDLE DIA.		A in. (mm)	B in. (mm)	C in. (mm)	D in. (mm)	E in. (mm)	F in. (mm)	G in. (mm)	H in. (mm)	MAX PANEL THICKNESS in (mm)	MIN. LOOP TENSILE lbs (N)	CROSS- SECTION	WEIGHT lbs/100pcs (g)
	MIN in (mm)	MAX in (mm)												
PLP1.5I	.06 (1.5)	1.25 (31.8)	.045 (1.1)	.135 (3.4)	.350 (8.9)	.236 (6.0)	.270 (6.9)	6.13 (156)	.260 (6.6)	.187 (4.7)	.093 (2.4)	40 (178)	INTERMEDIATE	.17 (77)

NOTES:

- * 1) SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE
- 2) SEE DRAWING 22-26803(A) FOR PLP1S, PLP1.5S & PLP2S.

										TITLE						
										STRAP, PUSH MOUNT – PLP						
										CUSTOMER DRAWING						
										ITEM REVISION NAME			10B0150X/04			
										DATASET FILE NAME			10B0150X_DC_PLP1.5I/04A			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]					MATERIAL:	
										.X ± .1 (2.5) .XXX ± .020 [.51] .XX ± .02 [.51] ANGLES ±					NYLON 6.6	
										 THIRD ANGLE PROJECTION					DRAWING NUMBER:	
4	01.06.15	BDK	MPH	JADE	UPDATED TITLE BORDER AND UPDATED NOTES				SS-26888						SS-26888	
REV	DATE	BY	CHK	APR	DESCRIPTION				ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1		SIZE
										RAM	2-1-94	HVP	NONE			A

2

1

91701000A/16