






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	52		U3	Obsolescence of PN 1-640136-0, 1-640136-1, 1-640136-2, 1-640136-5, 1-640136-6, 1-640136-8.	01SEP2014	TJ	JK



RECOMMENDED LAYOUT PATTERN
FOR 1.575±0.191 [.0620±.0075] THICK
P.C. BOARD INCLUDING CIRCUITRY

△	OBSOLETE	87.83[3.458]	92.08[3.625]	88.11[3.469]	22	2-640136-2
	OBSOLETE	71.96[2.833]	76.20[3.000]	72.24[2.844]	18	1-640136-8
	OBSOLETE	64.01[2.520]	68.25[2.687]	64.29[2.531]	16	1-640136-6
	OBSOLETE	60.05[2.364]	64.29[2.531]	60.33[2.375]	15	1-640136-5
	OBSOLETE	48.13[1.895]	52.37[2.062]	48.41[1.906]	12	1-640136-2
	OBSOLETE	44.17[1.739]	48.41[1.906]	44.45[1.750]	11	1-640136-1
	OBSOLETE	40.21[1.583]	44.45[1.750]	40.49[1.594]	10	1-640136-0
		36.25[1.427]	40.49[1.594]	36.53[1.438]	9	640136-9
		32.26[1.270]	36.50[1.437]	32.54[1.281]	8	640136-8
	OBSOLETE	28.30[1.114]	32.54[1.281]	28.58[1.125]	7	640136-7
		24.33[.958]	28.58[1.125]	24.61[.969]	6	640136-6
△	OBSOLETE	20.37[.802]	24.61[.969]	20.65[.813]	5	640136-5
		16.38[.645]	20.62[.812]	16.66[.656]	4	640136-4

8.46[.333]		12.70[.500]		8.74[.344]		2		640136-2					
C		B		A		NO OF CIRCUITS		PART NO.					
THIS DRAWING IS A CONTROLLED DOCUMENT.				OWN K. SALMON 2-20-92 CHK R. SWING 2-20-92 APVD W. LONG 4-24-92		 TE Connectivity							
DIMENSIONS: MM [INCHES]		TOLERANCES (UNLESS OTHERWISE SPECIFIED):		NAME		HOUSING, EDGE CONNECTOR, BIFURCATED LEAF							
		0 PLC ± -		PRODUCT SPEC 108-1020 APPLICATION SPEC 114-1015		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
		1 PLC ± -											
		2 PLC ± 0.13 [.005]											
		3 PLC ± -											
4 PLC ± -		5 PLC ± -		6 PLC ± -		7 PLC ± -		8 PLC ± -		9 PLC ± -		10 PLC ± -	
MATERIAL		FINISH		WEIGHT		A1		00779		C-640136		—	
POLYESTER, UL94V-0 (NATURAL)		—		—		—		—		—		—	
CUSTOMER DRAWING				SCALE		5:1		SHEET		1 OF 1		REV 1/3	