





2/3

Major diameter	[mm]	10.0	0/-0.18
Minor diameter	[mm]	7.5	

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: 2:1		
								Material: 1.4021 		
3	revise chart	21.06.17	A.S.				Name	Date	THREADED SPINDLE	
2	revise drawing	08.06.17	A.S.				DRN	J.W.		29.06.2011
1	material info	31.03.14	J.D.				CHKD	S.R.	29.06.2011	ZST10-2-300-1
REV	DESCRIPTION	DATE	DRN							