




SOLDER TERMINAL

ELECTRICAL

- DIELECTRIC STRENGTH 1000VAC
- INSULATION RESISTANCE 1G Ohms
- CONTACT RESISTANCE (INITIAL) 50m Ohms
- CURRENT RATING:-
 - @ 32VAC RESISTIVE 400mA
 - @ 50VDC RESISTIVE 100mA
 - @ 125VAC RESISTIVE 125mA
- LIFE (MINIMUM) 500,000 CYCLES
- SWITCHING POWER (MAXIMUM) 16VA AC

MECHANICAL

- TRAVEL (NOMINAL) 2.3mm
- LIFE (MINIMUM) 1,000,000 CYCLES
- OPERATING FORCE (NOMINAL) 3N
- ENVIRONMENTAL & PHYSICAL
 - INGRESS PROTECTION IP67
 - SHOCK 100G
 - OPERATING TEMP RANGE -55°C TO +125°C
 - CONTACTS GOLD PLATED-PALADIUM NICKEL

CAD SYSTEM No: 1			DIRECTORY NAME:			CAD DRAWING No: 599089TA.DWG			A3			
ISS.	CHANGE NOTE No.	DATE	DRAWN	ISS.	CHANGE NOTE No.	DATE	DRAWN	MATERIAL & SPEC.				
A	ECN86104	4.6.96	BV									
ITW Switches © 1996 Licon Switches, Chicago Switch, RC/UID Switches								SEE GA.				
The Copyright in this drawing and in the article appearing hereon is the property of ITW Switches and no reproduction in whole or in part of the drawing or the articles shown may be made without prior written permission.												
DRAWN	CHKD.	APPR.	SCALE	DATE	TITLE	DRAWING No.			ISS.			
BV	RE	KS	5:14.6.96		MINIATURE SEALED RAISED/ROUND BEZEL P/B	59-900089			A			