



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	02/28/18	JLABOY
			D.CUI



HIGH FLEX, CAT5e CABLE
 CONDUCTOR: FOUR TWISTED PAIR, 26AWG STRANDED TINNED COPPER
 SHIELD: TINNED COPPER BRAIDED
 CABLE JACKET: PU, DARK BLUE, NOM DIA .228[5.80]
 OPERATING TEMPERATURE RANGE: -20°C TO +80°C



PART NUMBER	LENGTH	
	FEET	METERS
TRG516-P6D-1M	3.28	1.0
TRG516-P6D-2M	6.56	2.0
TRG516-P6D-3M	9.84	3.0
TRG516-P6D-4M	13.12	4.0
TRG516-P6D-5M	16.41	5.0
TRG516-P6D-10M	32.82	10.0

- NOTES:**
1. PLUG CONFORMS TO TIA-1096
 2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
- REGULATORY COMPLIANCE:**
 CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		50 HIGH STREET NORTH ANDOVER, MA 01845
	DRAWN BY D.CUI	02/03/18		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13]	CHECKED BY W.LI	02/03/18	CATEGORY TELECOM/MODULAR	
	APPROVED BY S.PAN	02/03/18	PRODUCT DESCRIPTION C5e GigE S/UTP 26STR PUR HIFLX DBLU	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
REF	SCALE: NONE	CAD FILE: TRG516-P6D.SLDDRW	DWG. NO. TRG516-P6D	REV. A