



20 ~ 160CKT



キャリアテープ幅：24mm～72mm
CARRIER TAPE WIDTH : 24mm-72mm


200CKT



キャリアテープ幅：88 mm
CARRIER TAPE WIDTH : 88 mm

注)
NOTES

- 製品番号 55091-**-72 の詳細寸法については、SD-55091-006 を参照下さい。
IN THE PACKAGE , PART NO. 55901-**-72 DETAILED DIMENSIONS , SEE SD-55091-006.
- 梱包数量 : 1000 個/リール
NUMBER OF CONNECTORS : 1000 PCS/REEL
- リードテープ長さ
LEAD TAPE LENGTH




- 材料
MATERIAL
キャリアテープ : ポリプロピレン (PP) : 20 ~ 160 極
ポリスチレン (PS) : 200 極

CARRIER TAPE : POLYPROPYLENE (PP) : 30, 40, 50, 80, 90, 120, 140, 160, 240CKT
POLYSTYRENE (PS) : 20, 60, 70, 100, 180, 200CKT

トップテープ : PET, PE, PEF
TOP TAPE : PET, PE, PEF
リール : キャリアテープ幅 24mm～72mm : 紙
REEL : CARRIER TAPE WIDTH 24mm-72mm : CARD BOARD
キャリアテープ幅 88mm : ポリスチレン
CARRIER TAPE WIDTH 88mm : POLYSTYRENE

- 本製品は55091-***4の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 55091-***4.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex				
mm		-										
GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± 0.0° 4 PLACES ± 0.2 3 PLACES ± 0.25 2 PLACES ± 0.3 1 PLACE ± 0.2 0 PLACES ± DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				EC NO: 175909				55091-**72 TAPING PACKAGE -LEAD FREE-				
				DRWN: RMIYAMOTO 2018/03/16								
				CHK'D: KSASAKI 2018/05/01								
				APPR: RTAKEUCHI 2018/05/01				PRODUCT CUSTOMER DRAWING				
				INITIAL REVISION:				DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
				DRWN: HKAWABATA 2004/03/31				SD-55091-007		PSD	001	F
APPR: MSASAO 2004/04/01												
THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER				
		A3-SIZE		55091		SEE CHART		GENERAL MARKET				
								SHEET NUMBER				
								1 OF 3				



DOCUMENT STATUS	P1	RELEASE DATE	2018/05/01	09:36:11
-----------------	----	--------------	------------	----------

FORMAT: master-B-prod-A3
REVISION: 14
DATE: 2018/01/18

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
CURRENT REV DESC:		molex							
DIMENSION UNITS		SCALE		55091-**72 TAPING PACKAGE -LEAD FREE-					
mm		-							
GENERAL TOLERANCES (UNLESS SPECIFIED)									
ANGULAR TOL ± 30°				EC NO: 175909					
4 PLACES ± 0.2				DRWN: RMIYAMOTO		2018/03/16			
3 PLACES ± 0.25				CHK'D: KSASAKI		2018/05/01			
2 PLACES ± 0.3				APPR: RTAKEUCHI		2018/05/01		PRODUCT CUSTOMER DRAWING	
1 PLACE ± 0.2				INITIAL REVISION:		DOCUMENT NUMBER		DOC TYPE	DOC PART
0 PLACES ±				DRWN: HKAWABATA		SD-55091-007		PSD	001
				APPR: MSASAO		2004/04/01		F	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SHEET NUMBER	
						A3-SIZE		55091	
				SERIES		MATERIAL NUMBER		CUSTOMER	
						SEE CHART		GENERAL MARKET	
								3 OF 3	

F

E

D

C

B

A

F

E

D

C

B

A

引き出し方向
PULL OUT DIRECTION

Y

12±0.1

(6.2)
(5.5)

D

A

C

56巾テープ
56 WIDTH TAPE

44巾テープ
44 WIDTH TAPE

32巾テープ
32 WIDTH TAPE

24巾テープ
24 WIDTH TAPE

トップテープ
TOP TAPE

コネクタ中心
ø OF CONNECTOR

B

A

B

(0.6)

7±0.3

55091-**72
CONNECTOR

断面 Y-Y
SECTION Y-Y

累積ピッチ : 40±0.2
ACCUMULATIVE
PITCH : 40±0.2

Y

Ø1.5^{+0.1}_{-0.1}

(5.2)

(2)

4±0.1

+0.15
0.2 -0.05

1.5^{+0.1}₀

(R0.75)

A部詳細

55091-**74
MODEL NO

56.4	52.4	56 ^{+0.3}	26.2	38.9	55091-1074	100	○
				35.8	▲ -0974	90	○
44.4	40.4	44 ^{+0.3}	20.2	32.6	-0874	80	○
				29.4	-0774	70	○
				28.8	-6874	68	—
				26.2	-0674	60	○
				23.1	-0574	50	○
32.4	28.4	32 ^{+0.3}	14.2	19.9	▼ -0474	40	○
				16.7	-0374	30	○
24.4	—#—	24 ^{+0.3}	11.5	13.5	55091-0274	20	○
E	D	C	B	A	MATERIAL NO.	極数 NO. OF CKTS.	層数 NO. OF LYS.

REVISED
EC NO: J2009-0365
DRWN:WABEI
CHKD:THARUYAMA
APPR:NUKITA

DESCRIPTION
2008/08/06
2008/08/07
2008/08/07

GENERAL TOLERANCES
(UNLESS SPECIFIED)

10 UNDER	±0.2
10 OVER 30 UNDER	±0.25
30 OVER	±0.3
ANGULAR	±3°

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY

DRAWN BY
KAWABATA

CHECKED BY
KTOJO

APPROVED BY
MSASAO

MATERIAL NO.

SIZE
A3

DATE
'04/03/05

DATE
'04/03/05

DATE
'04/03/05

SCALE

DESIGN UNITS
METRIC

THIRD ANGLE
PROJECTION



55091-**72 TAPING
PACKAGE
-LEAD FREE-

MOLEX INCORPORATED

DOCUMENT NO.
SD-55091-007

SHEET NO.
2 OF 3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION



	72.4	68.4	72 ^{+0.3}	34.2	58.0	55091-1674	160	○
					51.6	55091-1474	140	○
55091-**-74					45.3	55091-1274	120	○
MODEL NO.	E	D	C キャリアテープ幅 CARRIER TAPE WIDTH	(B)	(A)	MATERIAL NO.	極数 NO. OF CKTS.	庫容対応 AVAILABILITY

REVISED	EC NO: J2009-0365	2008/08/06	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
	DRWN:NABEI	2008/08/07				MM ONLY		---		METRIC			
	CHKD:THIRUYAMA					DRAWN BY DATE		TITLE					
	APPR:NUKITA	2008/08/07				CHECKED BY DATE							
						APPROVED BY DATE							
				10 UNDER	±0.2	KAWABATA	'04/03/05	55091-**-72 TAPING					
				10 OVER 30 UNDER	±0.25	KTOJO	'04/03/05	PACKAGE					
				30 OVER	±0.3	MSASAO	'04/03/05	-LEAD FREE-					
				ANGULAR	±3 °	MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-55091-007		3 OF 3			
						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							