






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
D	ECN 8473 :UPD DWG TO MATCH NEW DESIGN, ADD NOTES 4 INFO	09/02/16	D.CUI
E	ECN 8516:UPD NOTES AND PIN-OUT, ADD A CONFIG TABLE	10/20/16	D.CUI
F	ECN 8803: REMOVE CONFIG VIEW AND NOTES 3 FROM THE DWG	06/06/17	D.CUI
G	ECN 8915:ADD COLOR CODE TO WIRES	9/08/17	D.CUI



"J1"  
USB SERIES "B"  
WATERPROOF  
JACK

WIRING MAP	
PIN#	COLOR
1	RED (PT 1945C)
2	WHITE (RAL 9003)
3	GREEN (PT 328C)
4	BLACK (PT BLACK 6C)
SHELL	GRAY (PT 421C)



- NOTES:**
- 1.COMPONENT ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  - 2.L-COM LOGO STYLE MAY VARY PER L-COM SPECIFICATION
  - 3.INGRESS PROTECTION RATING IS IP67 (J1 ONLY ,MATED)
  - 4.COMPONENT ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONS ARE IN INCHES [mm]  
OVERALL CABLE LENGTH TOLERANCE:  
≤12 [305] = +1 [25] / -0  
>12 [305] ≤60 [1524] = +2[51] / -0  
>60 [1524] ≤120 [3048] = +4 [102] / -0  
>120 [3048] ≤300 [7620] = +6 [152] / -0  
>300 [7620] = +5% / -0%  
ALL OTHER DIMENSIONAL TOLERANCES:  
.X = ±.2 [5.08]  
.XX = ±.02 [5.1]  
.XXX = ±.005 [1.3]

APPROVALS	DATE
DRAWN BY J. KIEZULAS	10/31/2005
CHECKED BY M. LAHEY	10/31/2005
APPROVED BY R. CARRICK	10/31/2005



CATEGORY		USB	
PRODUCT DESCRIPTION			
USB WATERPROOF SERIES B BULKHEAD TO BLUNT END			
SIZE	FSCM NO.	DWG. NO.	REV.
<b>B</b>	<b>43321</b>	<b>WPUSBBF</b>	<b>G</b>
SCALE: 1:1		CAD FILE: WPUSBBF.SLDDRW	SHEET 1 OF 1