
FEMALE END VIEW	
3 - 1	
enro Fast.	

_								
	SPECIFICATIONS							
	HOUSING MATERIAL/PLATING	NYLON/BLACK						
	CONTACT MATERIAL/PLATING	BRASS/OPTALLOY (CuSnZn)						
	COUPLING NUT MATERIAL/COLOR	NYLON/BLACK						
	RATED CURRENT [A]	4.0 A						
	RATED VOLTAGE [V]	60 V						
	MAXIMUM WIRE SIZE	18 AWG						
	CABLE GRIP RANGE	4-8mm						
	TEMPERATURE RATING	-25°C to +85°C (-13°F to +185°F)						
	PROTECTION CLASS	MEETS IEC IP67						



SOURCE DRAWING - FOR REFERENCE ONLY

					RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED. High Technology Sensors and Automatical Properties of the Properties of Technology Sensors and Automatical Properties of Technology Sensors and Sen		y Sensors and Automation Controls	3000 CAMPUS MINNEAPOLIS, MN 1-800-544- (763) 553-7 (763) 553-0 turck.com	N 55441 -7769 7300 0708 fax	
					SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	APVD UNIT OF ME	DATE 05/04/99 SCALE 1=1.0 EASUREMENT	B 8151-0/PG9		
				FINISH	CONTACT TURCK	MILLIM	ETERS	IDENTIFICATION NO. U656	5	REV	
E	UPDATE CONTACT MATERIAL	KMY	03/20/1	3 41634	SEE SPECIFICATIONS	FOR MORE INFORMATION					
REV	DESCRIPTION	BY	DATE	ECO NO.			DO NOT SCALE	THIS DRAWING	FILE: U6565	SHEET	г 1 OF 1