




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	30DEC2015	DL	CW


D




H10BP-T3-M
T2071104101-000
DOCKING FRAME FOR HMN INSERTS_FLOATING
3 MODULES

NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
FLAMMABILITY: UL94V-0
MATING CYCLES: 500




注释:
1. 技术参数:
绝缘材料: PC
阻燃等级: UL94V-0
插拔次数: 500次



PANEL CUT OUT



SPACING OF TWO PANELS
AT CLOSE STATUS



OTHER SPEC REFER TO
PN T2071104101-000

H10BP-T3-F
T2071104201-000
DOCKING FRAME FOR HMN INSERTS_FIXED
3 MODULES

T2071104201-000	H10BP-T3-F DOCKING FRAME FOR HMN INSERTS_FIXED HMN塑胶框架_固定端
T2071104101-000	H10BP-T3-M DOCKING FRAME FOR HMN INSERTS_FLOATING HMN塑胶框架_浮动端
PART NUMBER 料号	PART DESCRIPTION 描述

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI 30DEC2015	TE Connectivity			
DIMENSIONS: mm		CHK CHRIS WANG 30DEC2015				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD XU XIANG 30DEC2015	NAME H10BP-T3-M/F DOCKING FRAME FOR HMN INSERTS 3 MODULES			
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC 108-137168 APPLICATION SPEC 114-137168 WEIGHT -	SIZE A2	CAGE CODE -	DRAWING NO C-T2071104X01000	RESTRICTED TO -
MATERIAL -		CUSTOMER DRAWING	SCALE 1:1	SHEET 1	OF 1	REV A

A

A