



TABLE 1

MODEL NUMBER	"L"	MARKER 
UPCMWX-12-75	12	UPCMWX-12-75 14949 #####
UPCMWX-18-75	18	UPCMWX-18-75 14949 #####
UPCMWX-24-75	24	UPCMWX-24-75 14949 #####
UPCMWX-36-75	36	UPCMWX-36-75 14949 #####
UPCMWX-48-75	48	UPCMWX-48-75 14949 #####

WIRING DIAGRAM



NOTES: UNLESS OTHERWISE SPECIFIED.

1. WORKMANSHIP PER IPC/WHMA-A-620, CLASS 3 SECTION 13.


-  2. TOLERANCE PER IPC-WMHA-620, SECTION 11.1.

3. TESTING:

- 3.1 CONTINUITY
3.2 DWV: 1500 VRMS

4. BEND RADIUS (MIN): 1.0

-  5. MARKER:
5.1 MARKED PER TABLE 1
5.2 ##### = LOT CODE

 This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not to be traced or copied without permission and is returnable upon demand. INTERPRET DRAWING ACCORDANCE WITH ASME Y14.5-2009.		TROMPETER	
	RoHS2 2011/65/EU	Title: CABLE ASSEMBLY, TCC-75-2 PATCH PLUG TO BNC PLUG	
	UNLESS OTHERWISE SPECIFIED UNITS: INCH 	Model No. UPCMXX-XX-75	
	SIZE A	DO NOT SCALE DRAWING	Workmanship Std. SEE NOTES