





beispielhafte Darstellung UNI IRIS Dicht Verschraubung für EMV Pg29
exemplary drawings universal IRIS cable protection for EMC Pg29

09 62 000 5023	Pg11	4-6,5	2,5-6,5	20
09 62 000 5024	Pg11	6,5-9,5	3,5-8,5	20
09 62 000 5003	Pg13,5	6,5-9,5	2,5-6,5	22
09 62 000 5004	Pg13,5	9-13	6,5-10,5	22
09 62 000 5005	Pg16	6,5-9,5	3,5-8	24
09 62 000 5006	Pg16	9-13	4,5-8	24
09 62 000 5007	Pg21	11,5-15,5	9,5-13,5	30
09 62 000 5008	Pg21	14-18	10,5-14,5	30
09 62 000 5009	Pg29	17-20,5	15-20	40
09 62 000 5010	Pg29	20-25	15-20	40
09 62 000 5011	Pg36	24-28	18-25,5	50
09 62 000 5012	Pg36	27-32	24-31	50
Bestell Nr Part No	Gewinde thread	Kabel/cable min.- max.	Schirm/shield min.- max.	SW



All Dimensions in mm
 Original Size DIN A 4

Techn. Character.

Nicht tolerierte Maße/Free size tolerances

	Dat.	Name	Maßstab/Scale
Detail.	24.10.08	Bor	2:1
Insp.		Be	
Stand.			

**UNI IRIS Dicht Verschraubung
 für EMV**
universal IRIS cable protection for EMC

HARTING Electric GmbH & Co. KG
 D-32339 Espelkamp



TB 09 62 000 50..

Sub. TB 09 62 000 50.. v. 23.10.96

Blatt/ page