





Applicable cable	
Items	Applicable condition
Conductor size	AWG 28-26
Insulation O.D.	Ø0.95 to 1.05 mm
Braid Shield	Tin plating
Sheath O.D.	Ø6.3mm - Ø7.2mm


Contact material: copper alloy
Contact area: Gold 0.2µm min.
Wiring area: Gold 0.03µm min.
Under plating: Nickel 2µm min.

	All Dimensions in mm Original Size DIN A4	Scale 2:1	Free size tol.		Ref.	
				Sub.		
	All rights reserved	Created by POPESCU	Inspected by PRIESTER	Standardisation HOFFMANN	Date 2018-08-27	State Final Release
	Department EL PD	Title ix Industrial 10B-1 plug SL-I26				Doc-Key / ECM-Nr. 100747810/UGD/000/B 500000138273
	HARTING Electronics GmbH D-32339 Espelkamp	Type TB	Number 09451819001			Rev. B


Shield Shell delivery form




Product Structure




Mating condition (2:1)



Plug Unit



		All Dimensions in mm Original Size DIN A4		Scale 1:1		Free size tol.		Ref.							
								Sub.							
		All rights reserved		Created by POPESCUD		Inspected by PRIESTER		Standardisation HOFFMANN		Date 2018-08-27		State Final Release			
HARTING Electronics GmbH D-32339 Espelkamp		Department EL PD		Title ix Industrial 10B-1 plug SL-I26								Doc-Key / ECM-Nr. 100747810/UGD/000/B 500000138273			
				Type TB		Number 09451819001						Rev. B		Page 2/2	