



CODE No.	CONTACT	A	B	C	D	E	F	G
CL537-0028-7-86	20	7.2	4.5	5.3	5.7	6.6	5.3	8.1
CL537-0030-9-86	30	9.7	7.0	7.8	8.2	9.1	7.8	10.6
CL537-0031-1-86	36	11.2	8.5	9.3	9.7	10.6	9.3	12.1
CL537-0032-4-86	40	12.2	9.5	10.3	10.7	11.6	10.3	13.1
CL537-0034-0-86	50	14.7	12.0	12.8	13.2	14.1	12.8	15.6
CL537-0036-5-86	60	17.2	14.5	15.3	15.7	16.6	15.3	18.1

						7		PS		CLEAR (REINFORCEMENT COLLAR)	
						6		PS		BLACK (PLASTIC REEL)	
2	PHOSPHOR BRONZE	CONTACT AREA:GOLD PLATED 0.2#m min LEAD AREA:GOLD PLATED 0.015#m MIN OTHERS(UNDER PLATING):NICKEL PLATED 2#m min				5		POLYESTER		CLEAR (COVER TAPE)	
						4		PS		CLEAR (EMBOSSD CARRIER TAPE)	
1	POLYAMIDE	UL94V-0, NATURAL (BEIGE)				3		BRASS		TIN PLATED 2#m MIN (UNDER PLATING):NICKEL 1#m MIN	
NO.		MATERIAL		FINISH , REMARKS		NO.		MATERIAL		FINISH , REMARKS	
UNITS mm				SCALE 5 : 1				COUNT 1		DESCRIPTION OF REVISIONS DIS-H-00001707	
								DESIGNED SH. HOSODA		CHECKED TS. MIYAZAKI	
										DATE 16. 06. 10	
 HIROSE ELECTRIC CO., LTD.		APPROVED		KH. IKEDA		12. 11. 06		DRAWING NO. EDC3-163509-77			
		CHECKED		YH. MICHIDA		12. 11. 06		PART NO. DF12(3. 5)-*DP-0. 5V(86)			
		DESIGNED		YN. SAKAMOTO		12. 11. 06		CODE NO. CL537			
		DRAWN		YN. SAKAMOTO		12. 11. 06		 1/2			

