

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT INVENTORY NUMBERING SYSTEM

HSTTV A 12 . 48 . Q

PACKAGE QUANTITY: Q = 25
S = 5

TUBE LENGTH IN INCHES

TUBING SIZE- EXPANDED I.D.

FLEXIBLE. ADHESIVE LINED THIN WALL HEAT SHRINK TUBING.

PANDUIT PART NUMBER	Min. Exp. I.D In. (mm)	Max. Rec. I.D In. (mm)	NOMINAL REC WALL THICKNESS In. (mm)
HSTTV A12	.125 (3.2)	.063 (1.6)	.021±.004 (.53±.102)
HSTTV A19	.187 (4.8)	.093 (2.4)	.023±.004 (.58±.102)
HSTTV A25	.250 (6.4)	.125 (3.2)	.029±.005 (.74±.127)
HSTTV A38	.375 (9.5)	.187 (4.8)	.029±.005 (.74±.127)
HSTTV A50	.500 (12.7)	.250 (6.4)	.030±.005 (.76±.127)
HSTTV A75	.750 (19.0)	.375 (9.5)	.035±.005 (.89±.127)
HSTTV A100	1.000 (25.4)	.500 (12.7)	.042±.007 (1.07±.178)
HSTTV A150	1.500 (38.1)	.750 (19.0)	.047±.008 (1.19±.203)

NOTES:

- SHRINK RATIO: 2:1
- SHRINK RATIOS ARE APPROXIMATIONS; PLEASE REFER TO TABLE 1 FOR THE EXACT MINIMUM EXPANDED AND MAXIMUM RECOVERED I.D.'S.
- MATERIAL: CROSSLINKED POLYOLEFIN WITH ADHESIVE
- COLOR: BLACK
- "ALL WARRANTIES, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. (USER IS RESPONSIBLE TO DETERMINE SUITABILITY OF PRODUCT FOR INTENDED USE.)"

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS

G00239K_PB_HSTTV A_00

PANDUIT

CORP. TINLEY PARK, ILLINOIS

FLEXIBLE ADHESIVE LINED
THIN WALL HEAT SHRINK
(HSTTV A)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
LGRAVITT

MAT'L:

SCALE NONE

DATE
5/14/03

SEE NOTES

DRAWING NO.

G00239KN

DWG
A
SIZE

R	5/14/03	LGG	INITIAL RELEASE	G00239KN	R		
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP