THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

REVISIONS									
REV.	DESCRIPTIONS	DATE	APPROVED						
_	CLASS A RELEASED	7/11/99							
А	UPDATED CONFIGURATION	1/1/16							

1. REPLACEMENT PROBE TIP, 5 mm, THREADED, FOR GENERAL PURPOSE AND GE SERIES OSCILLOSCOPE PROBES.

2. SPECIFICATIONS:

INSULATOR: POLYAMIDE (NYLON) CONTACT: BRASS, GOLD PLATED


3. RATING:


VOLTAGE: 300 V CAT II CURRENT: 1 A MAX.

TEMPERATURE: 0° C TO +50°C

CE DECLARATION OF CONFORMITY CONFORMS TO ROHS 2, ANNEX III 6(c) EXEMPTION.

4. STANDARD PACKAGING: INDIVIDUAL TIPS: 10 PCS. PER PACK.





— COLOR: 0 — BLACK

8 - GREY

THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	CONTRACT NO.			\ - T 4		-4:		22820 Savi Ranch Parkw	101
		TOLERANCES ARE: FRACTIONS DECIMALS ± 1/32 .XX ± .02 .XXX ± .005 DO NOT SCALE DRAWING		_		al Test	⊏ıe	ctronic	cs :	Yorba Linda, CA 92887-	
$\overline{ (\oplus)}$			APPROVALS	DATE	TITLE						
			drawn WDH	7/11/99	R	REPLACEMENT TIP, 5 mm, THREADED,					
		MATERIAL	CHECKED]	OSCILLOSCOPE PROBE					•
		FINISH	ENGR.		SIZE	CAGE CODE		DWG. NO.	D2	71140	REV.
NEXT ASSY	USED ON		DESIGN ACTIVITY		A 43F45			P2711A0			А
APPLICATION					SCALE	1:1				SHEET 1 OF	1