






1. THIS RCPT. IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308
2. MAX WIRE INSUL TO BE USED WITH THIS RCPT IS .054 DIA
3. METAL RETENTION CLIPS ARE INCLUDED IN INSERTS
4. PACKAGE MARKED M 24308/2-298F
5. THIS RCPT. WILL ACCEPT SIZE 22 SOCKET CONTACT M 24308/12 OR AMP # 204351

AMP PART NO. MARKED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS

UL/CSA DESIGNATION MARKED IN THIS AREA.

OBSOLETE	PHENOLIC, COLOR: BLACK	204524-2
	POLYPHENELYENE SULFIDE (PPS) GST-40F PER MIL-M-24519 OR GLASS FILLED POLYESTER TPES013G30 PER ASTM D5927 COLOR, BLACK	204524-1
	INSERT MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C. THOMAS CHK J.C. BALLEW III APVD D.J.M.	12-3-87 1-25-88 1-25-88	TE Connectivity	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± . 1 PLC ± . 2 PLC ± . 3 PLC ± .005 4 PLC ± . ANGLES ± .	NAME PRODUCT SPEC APPLICATION SPEC	AMPLIMITE RCPT. FOR SOCKET CONTACTS HI-DENSITY D CONN,SIZE 2, SERIES 90 WITH FLOAT BUSHINGS		
MATERIAL SEE CALLOUTS	FINISH SEE CALLOUTS	WEIGHT —	SIZE A1	CAGE CODE 00779	DRAWING NO 204526
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 1	REV P