

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

U

-

P

LTR

DESCRIPTION

DATE

DGN

APVD


P

REVISED PER ECO-11-005139

28MAR11

RK

HMR



FOR CONTINUOUS




5.8

4.6

FOR SINGLES

5.3

4.0



## NOTES:

## 1. WIRE RANGE

CONDUCTOR: 0.7mm<sup>2</sup> - 2.1mm<sup>2</sup>

INSULATION DIA: 2.3mm - 3.1mm

## 2. FOR CRIMPING DETAILS REFER

UTILUX CRIMP CHART No. H1972

|             |               |                           |             |
|-------------|---------------|---------------------------|-------------|
| LOOSE PIECE | NICKEL SILVER | RECEPTACLE, H1972B/150    | 1-1627057-9 |
| LOOSE PIECE | BRASS         | RECEPTACLE, H1972/10000   | 1-1627057-7 |
| REEL FORM   | NICKEL SILVER | RECEPTACLE, H1972B/R8000  | 1-1627057-5 |
| REEL FORM   | BRASS PRE-TIN | RECEPTACLE, H1972ET/R8000 | 1-1627057-6 |
| REEL FORM   | BRASS         | RECEPTACLE, H1972/R8000   | 1-1627057-4 |
| LOOSE PIECE | BRASS         | RECEPTACLE, H1972/150     | 1-1627057-1 |
| REMARKS     | MATERIAL      | DESCRIPTION               | PART No.    |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

W.RIEDE 28.10.04

CHK

H.THAH 28.10.04

APVD

W.RIEDE 28.10.04

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

ALL DIMENSIONS IN mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

DIMENSION (mm) TOLERANCE (mm)

LESS THAN 10 0.4



OVER 10 TO 30 0.5

OVER 30 TO 80 0.7

OVER 80 TO 250 1.0

ANGLES ±2°

MATERIAL

UNREELING DIRECTION  
FROM TOP OF REEL

TE Connectivity

RECEPTACLE, QC 6.3

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

C-1627057

-

CUSTOMER DRAWING

SCALE 5:1

SHEET 1 OF 1

REV P