
A standard in-line 4mm banana plug with a stainless steel contact spring. The large rear diameter of this plug will accept cables with a conductor of up 5,5mm (10 awg). The lead wire is held by soldering in a large solder bucket.

The product is also supplied with a large diameter insulating cover that accepts cables with a maximum outside diameter of 7,1mm. Silver plating Plug Body.

Dimensions



Material				
Contact spring	Stainless steel, BS302			
Plug body	Brass TR1 CZ 131			
Plug housing	Acetal,C 27021 R			
Body plating	Silver plating			
Rating	16 Amps			
Voltage	50 Volts MAX			

Part No.	Colour & Plug Plating		
579-0100	BLACK	(Silver Plated)	
579-0200	BLUE	(Silver Plated)	
579-0300	BROWN	(Silver Plated)	
579-0400	GREEN	(Silver Plated)	
579-0500	RED	(Silver Plated)	
579-0600	WHITE	(Silver Plated)	
579-0700	YELLOW	(Silver Plated)	



bes DEM 🔀	TH PR
//Alpha3	PR AN WI IS
APPROPRIEST DESCRIPTION	DE

ROPRIETARY AND CONFIDENTIAL:

EM Manufacturing is a division of Alpha 3 Manufacturing LTD DEM Manufacturing, Deltron Emcon House, Hargreaves Way, Sawcliffe Ind. Park, Scunthorpe, North Lincolnshire, DN15 8RF, UNLESS OTHERWISE DIMENSIONS ARE IN LINEAR & RADIAL NO DECIMAL PLAC 1 DECIMAL PLACE ANGULAR TOLERA

SPECIFIED	
MILLIMETRES FOLERANCE:	FINISH
CES±0.2mm	MATER
E ±0.1mm ES ±0.05mm	TH
ANCE: ±1°	ΔΡ

IF IN DOUBT ASK! DO NOT SCALE DRAWING!	AUTHOR Alex Yau		GENERAL SPECIFICATION		
STANDARD I	EDITOR DT FILE 579 SERIES iss 003		RIES iss 003		
TERIAL -	APPROVER	DT	PART		
THE FINISHED PRODUCT SHOULD BE CLEAN AND FREE FROM ALL LIQUIDS AND DEBRIS. SURFACES SHOULD BE OF UNIFORM	THIRD ANGLE PROJECTION	SHEET 1 OF 1	ISSUE/REV. 003	version 6	
APPEARANCE FREE FROM SHARP EDGES, BURRS AND CORROSION		SCALE 1:1 A4	RELEASED	EDIT DATE 23 Oct 2017	