



TABLE

ITEM NO	L
4070	2000mm±30mm
4070-3	3000mm±30MM

HEAT SEALED



1. CABLE: NO UL, 28AWG(7/0.127), TINNED AND STRANDED COPPER WIRE
 INSULATOR: PVC, ID: 0.85mm, CABLING: 7C+DRAIN WIRE
 SHIELD: AL/MY COVERAGE
 JACKET: PVC, COMPLIANCE ROHS, COLOR: BEIGE, O.D: 5mm

2. 2PCS CONNECTOR: D-SUB 9 WAYS FEMALE SOLDER TYPE CONNECTOR
 INSULATOR: P.B.T.+GLASS FIBER, COLOR: BLUE
 CONTACT: COPPER ALLOY, GOLD FLASH OVER NICKEL PLATED
 SHELL: NICKEL PLATED.

3. HOOD: PVC MOLDED TYPE WITH FOIL SHIELDED ON INNER
 ON INNER MOLD AND INJECTION OUTER MOLD WITH
 THUMB SCREW#4-40 UNC
 COLOR: BEIGE, COMPLIANCE ROHS

4 Fulfill ROHS Guideline

5 ELECTRONIC TEST

100% OPEN SHORT+MISS WIRE TEST

DRAWING

DB9PIN JACK(J1)	WIRE	DB9PIN JACK(J2)
2	=====	3
3	=====	2
4	=====	6
5	=====	5
6	=====	4
7	=====	8
8	=====	7
SHELL	DRAIN WIRE	SHELL