





NOTES:

- 1: FOR MATERIAL SPECIFICATION SEE
NOTE 1. ON SHEET 2.
- 2: FOR RECOMMENDED P.C.B. HOLE PATTERN,
PART No's AND UNSTATED DIMENSIONS
SEE SHEET 2.
- 3: PRODUCT SPEC.No.: PS-99020-0015.
- 4: THIS RIB IS NOT PRESENT ON
10 & 14 CKT PARTS.




MEASURE POINT
FOR GOLD PLATING
THICKNESS TYP.

MIN. GOLD PLATE (5.10)
AREA. 30

DETAIL A

DIMENSIONS FOR SELECTIVE
PLATING'S. SCALE 4:1



SECTION F-F

SEE DETAIL A.

REMOVED REFS TO COLOR STAMP EC NO: E2011-0063 DRWN: JCONNOR CHKD: APPR: EFOLAN	DESCRIPTION 2010/08/12 2010/08/25 2010/08/30	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION 			
				mm	INCH	DRAWN BY POB	DATE 1990/08/03	TITLE QF50 SRD HDR VT W/ELV					
			4 PLACES	± ---	± ---	CHECKED BY JDENNEHY	DATE 2004/11/24						
			3 PLACES	± ---	± .008	APPROVED BY JDENNEHY	DATE 2004/11/24						
			2 PLACES	± 0.20	± .008	MOLEX MOLEX INCORPORATED					DOCUMENT NO. SDA-90663E	SHEET NO. 1 OF 9	
			1 PLACE	± 0.20	± ---								
			ANGULAR ± 2 °			MATERIAL NO.							
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE SHEET 2							
						SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
			REV										

