



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	05/21/18	B.PUCHAASKI



DIMENSIONS ARE METRIC

PART NUMBER	LENGTH METER [FEET]
VHA00014-05M	.5 [1.64]
VHA00014-1M	1.0 [3.28]
VHA00014-2M	2.0 [6.56]
VHA00014-3M	3.0 [9.84]
VHA00014-5M	5.0 [16.40]



**NOTES:**

- 100% MAC TO HDTV 1080P TESTING.
- COVER FOR HDMI A/M BOX, ABS, BLACK
- COVER FOR DP, ABS, BLACK
- INNER MOLDING, PE, COLOR: WHITE
- SR PVC 45P, COLOR: BLACK
- CONNECTOR HDMI + PCB 4K\*2K 171 SCHEME, SOLDER TYPE WITH COVER, PIN: GOLD FLASH, SHELL: NI PLATED
- CONNECTOR DISPLAYPORT 20P M SOLDER TYPE WITH COVER, PIN: GOLD FLASH, SHELL: NI PLATED
- CABLE: UL20276, 32AWG(7/0.08T\*1P+D+AL+MYLAR) \* 5P+7/0.10T\*1C+7/0.08T\* \*4C+AL+ADB 16/7/0.12] \*1C OD+5.0±0.15MM, JACKET COLOR:BLACK, LSZH
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		50 HIGH STREET NORTH ANDOVER, MA 01845							
	DRAWN BY B.PUCHAASKI	05/21/18		CATEGORY	AUDIO VIDEO						
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.3]	CHECKED BY J.LABOY	05/21/18		PRODUCT DESCRIPTION							
	APPROVED BY B.GATES	05/21/18		HDMI TO DP LSZH							
PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	<table border="1"> <tr> <td>SIZE</td> <td>FSCM NO.</td> <td>DWG. NO.</td> <td>REV.</td> </tr> <tr> <td><b>A</b></td> <td><b>43321</b></td> <td>VHA00014</td> <td><b>A</b></td> </tr> </table>	SIZE	FSCM NO.	DWG. NO.	REV.	<b>A</b>	<b>43321</b>	VHA00014	<b>A</b>
SIZE	FSCM NO.	DWG. NO.	REV.								
<b>A</b>	<b>43321</b>	VHA00014	<b>A</b>								
SCALE: NONE		CAD FILE: VHA00014.SLDDRW		SHEET 1 OF 1							