

	CE2011/65/EU(RoHS DIRECTIVE)					UNLESS OTHERWISE SPECIFIED,	APPROVALS	DATE			H STREET	
А						DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: \$12 [305] = +1 [25] / -0	DRAWN BY JYOU CHECKED BY	09/12/2018		nokin Ar	1845	
		5	Nut	Brass	NICKEL PLATE	>12 [305] <60 [1524] =+2 [51] / -0 >60 [1524] ≤120 [3048] =+4 [102] / -0 >120 [3048] <300 [7620] =+6 [152] / -0 >300 [7620] =+5% / -0%	BZHANG APPROVED BY	09/12/2018		oaxial		A
		4	Washer	Brass	NICKEL PLATE		SPAN	09/12/2018	PRODUCT DESCRIPTION			1
			Pin	BeCu	GOLD PLATE	ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ±.02 [.51] .XXX = ±.005 [.13]	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES		Ultra Tiny BNC Bulkhead Jack to Jack			
		2	Insulator	PTFE	None		MAY VARY		Adapter 75 Ohm, Isolated Type			
		1	Body	Brass	NICKEL PLATE		COLOR VARIATIONS MAY OCCUR		SIZE FSCM NO. DWG. NO A 43321	V7C00018	A REV.	
		ITEM	Description	Material	Finish	$\qquad \qquad $			SCALE: NONE CAD FILE: V7C00	CAD FILE: V7C00018.SLDDRW SHEET		Į
	8 7		6		5	↑ 4	3		2	1		