







REVISION			
SYM	DESCRIPTION	DATE	APPROVAL

请确认后签回此图纸!



1500+20mm




CABLE MARKING: H05VV-F 3G0.75mm² <VDE> N19626 CCC A030116 No.2003010105097406 60227 IEC 53(RVV) 300/500V 3X0.75mm² HIGH PROJECT

CABLE COLOR: BLUE

PRO-ELEC

UNLESS SPECIFIED ALL DIMENSIONS ARE
IN MM TOLERANCE ON:
FRACTION: DECIMALS: +/ - 0.10 ANGLE:

SHEET:	1 OF 1	DWG SIZE:	A4
SCALE:	N. T. S	ISSUE NO.	A
DRAWER	guo	DATE.	2019/04/08
REVIEW		DATE.	
APPROVAL.		DATE.	



CUSTOMER NAME:	
CUSTOMER ORDER NO:	- - -
QTY REQ'D PER UNIT:	1

CUST PART NO:	PL15156
DRAWING NO:	H8-0.5ALVW-C10
MODEL NO:	