





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	11/26/2018	JYOU
B	ECN 9837: REVISE DRAWING DIMENSIONING AND FORMAT	05/02/2019	DFRISIELLO



NOTES:

- ALL DIMENSIONS ARE FOR REFERENCE ONLY.

<div>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</div> <div>OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%</div> <div>ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [5.1] .XXX = ±.005 [1.3]</div>	APPROVALS	DATE	<div><div><div>L-com</div><div>Global Connectivity</div></div><div>50 HIGH STREET NORTH ANDOVER, MA 01845</div></div>			
	DRAWN BY JYOU	10/31/2018	CATEGORY 19" RACKS			
	CHECKED BY BGATES	10/31/2018				
	APPROVED BY BGATES	10/31/2018				
<div>PROJECTION</div> <div></div>	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION L-COM VERTICAL 19" WALL MOUNT RACK 2U			
	COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321	DWG. NO. RP00002-2	REV. B
			SCALE: NONE	CAD FILE: RP00002-2.SLDDRW	SHEET 1 OF 1	