



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	6	PRODUCTION ISSUE	31JAN2019	PNT	MT

a) Part as supplied.



b) Part after unrestricted recovery.



DIMENSIONS in millimetres
[in inches, for reference]

	H		J		P	R	S	T	U	JO	HW	JW	X	Y
Part No.	Min	Max	Min	Max	±10%	±10%	±10%	±10%	±10%	±10%	±20%	±20%	±20%	±20%
	a	b	a	b	b	b	b	b	b	b	b	b	b	b
202K232	25 [.98]	13.8 [.54]	8.0 [.31]	3.3 [.13]	55 [2.17]	28 [1.10]	3.0 [.12]	1.0 [.04]	15 [.59]	16 [.63]	1.8 [.07]	0.5 [.02]	24 [.94]	23 [.90]

DIMENSIONS:

mm [INCHES]

DWN

PRAVEEN N T

31JAN2019

MATERIAL

SEE SHEET 2

FINISH

—

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

CHK

N NAGAR

31JAN2019

APVD

M TAYLOR

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

NAME

MOULDED BOOT, STRAIGHT, WITH LIP

SIZE

A4

CAGE CODE

00779

DRAWING NO

C-202K232-XX-0

RESTRICTED TO

—

CUSTOMER DRAWING


SCALE

DNS

SHEET

1 OF 2

REV 6



RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

TE Connectivity Ltd.

COPYRIGHT

©

THIS DRAWING IS UNPUBLISHED.

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES ± —

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

COMPATIBILITY CHART

Material Dash Number	Material Description	RT Spec	Coating Slash No.	Coating S No.
—3	POLYOLEFIN, SEMI-RIGID	RT-301	/42,/86,/180	S1017; S1048; S1030
—4	POLYOLEFIN, FLEXIBLE	RT-1304	/42,/86,/180	S1017; S1048; S1030
—12	FLUOROELASTOMER, FLEXIBLE	RT-1312	N/A	N/A
—25	ELASTOMER, FLUID RESISTANT	RW-2070	/42,/86,/225	S1017; S1048; S1206

Ordering Information

202K232-XX/XX-0



Color designator

Adhesive Slash Number (if required see compatibility chart)

Material Dash Number (see compatibility chart)

Base Part Number

NOTES

- As supplied dimensions are for uncoated parts, when coating is added entry diameters will reduce by 1.5mm[.06]max.
- Potting Ports are optional, when specified by suffix "-00" they will be located as shown.


RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

COPYRIGHT - TE Connectivity Ltd.



THIS DRAWING IS UNPUBLISHED.

DIMENSIONS: mm [INCHES]	DWN PRAVEEN N T	31JAN2019	MATERIAL SEE SHEET 2	FINISH —
	CHK N NAGAR	31JAN2019	 TE Connectivity Ltd.	
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M TAYLOR	31JAN2019		
	PRODUCT SPEC —		SIZE A4	
	APPLICATION SPEC —		CAGE CODE 00779	DRAWING NO C-202K232-XX-0
	WEIGHT —		RESTRICTED TO —	
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —			SCALE DNS	
CUSTOMER DRAWING			SHEET 2 OF 2	REV 6