

NOTE:

1. MATERIAL

1.1 CABLE: 28AWG (7/0.12CU ± 0.008) * 6C + PVC JACKET.


1.2 CONNECTER: 6P6C MALE TYPE,
INSULATION: CLEAR POLYESTER, UL94V-2.
CONTACTS: BRASS, GOLD PLATED G/F

1.3 ALL COMPONENTS ARE RoHS COMPLIANT.

2. ELECTRICAL

2.1 100% OPEN AND SHORT TEST

PIN OUT		
CN1	CN2	COLOR
1	1	BLUE
2	2	BLACK
3	3	RED
4	4	GREEN
5	5	YELLOW
6	6	BROWN



SECTION A-A

Length	Tolerance
≤ 1000 mm	± 30 mm
$1000 < L \leq 5000$ mm	± 50 mm
$5000 < L \leq 10000$ mm	± 100 mm
$10000 < L \leq 20000$ mm	± 200 mm
20000 mm $< L$	± 500 mm

		Tolerance:		SCALE:	CUSTOMER:		PRO-SIGNAL		Approved by	
		X. ± 0.5		FREE						
		.X ± 0.3		UNIT:			CUSTOMER P/N:		COMPANY P/N:	
		.XX ± 0.10		mm					Checked by	
		Angle:		REV.:			DWG. No.:		TITLE:	
00 DESCRIPTION		2019-10-29		00			2019102901		TELEPHONE CABLE	
REV.	DESCRIPTION	DATE			SHEET	1/1			Design by	