



Panel Thickness: 0.79 - 1.98 top/1.57 bottom
Bottom Hole: 4.0 dia. +/-0.08
Top Hole: 4.75 dia. +/- 0.08

	Material		Customer Part No.	
	Finish		Web Ref No	