








GFCI MODULES ON ALL
20A INLET/ RECEPTACLES
REPLACEMENT CAT NO GFM20



NOTES:

- 1. INPUT/ OUTPUT VOLTAGE: 60A 120/208 3Ø VAC 60Hz
- 2. INCHES [mm]

INLET OR RECEPTACLE LOCATION	CATALOG NUMBER	
	SCSB0 STRAIGHT BLADE	SCTLO TWIST-LOCK
1,2,3,4,5,6	HBL53R61	HBL2310SW
7	HBL560B9R	HBL560B9R
8	HBL560R9W	HBL560R9W

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
ENCLOSURE	GALVANIZED STEEL	YELLOW POLYESTER PAINT
COVER	GALVANIZED STEEL	YELLOW POLYESTER PAINT
GASKET	CLOSED CELL NEOPRENE FOAM	
LEGS	HR STEEL	YELLOW POLYESTER PAINT
SCREW, #10 PAN HEAD	C1021 STEEL	CHROMATE/ ZINC
NUT, LOCKING	STEEL	ZINC PLATED
LABEL, PRODUCT	POLYESTER	CHROME COLOR

1	RELEASE PER DCN# 9145-2	1/4/02
SYM	REVISIONS	APP DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
SPIDER BOX 60AMP

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS	± 1/64	DR. BY PJT	APP. BY RDK
DECIMALS	± .005	TR. BY	SCALE NONE
ANGLES	± 2°	CHK'D BY RDK	DATE 1/4/02