
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.







*NOTE: UCACSR SHOWN IN PICTURE ABOVE. PICTURE FOR REFERENCE ONLY.

CABLE CUTTER BLADES

NOTES, UNLESS OTHERWISE SPECIFIED:

Panduit Cable Cutter Blades are designed to cut:

• Cuts Copper and Aluminum stranded conductor cables using Panduit Crimp, Cut and Punch Tools. Go to www.panduit.com for more information.

Size Chart:

Consult table below to select appropriate Panduit Cable Cutter Blade set for a specific cable outside diameter (O.D.), and compatible Panduit Crimp, Cut and Punch Tool:

Panduit P/N	For Cable OD Size	Compatible with Panduit Tool(s)
UC26	0 to 1.02" (0 to 26 mm)	CT-2920/CCP, CT-920CH/CCP
UC40	0 to 1.57" (0 to 40 mm)	CT-2920/CCP, CT-920CH/CCP,
	0 to 0.98" (0 to 25 mm)	CT-3001/CCP WITH UAM*
UCACSR	0 to 1.57" (0 to 40 mm)	CT-2920/CCP, CT-920CH/CCP,
	0 to 0.98" (0 to 25 mm)	CT-3001/CCP WITH UAM*

^{*} UAM for cutting blades sold separately.

Technical Information:

Consult table below for approximate package size and weight information for each product:

Panduit P/N	Weight	Package Size
UC26	0.35 lb (0.161 kg)	5" L x 3.5" W x 0.5" H
UC40	0.28 lb (0.126 kg)	[152.4 L x 88.9 W x 12.7 H] mm
UCACSR	0.41 lb (0.184 kg)	5" L x 3.5" W x 0.75" H
	` ,	[152.4 L x 88.9 W x 19.1 H] mm

Dimensions in [brackets] are in millimeters. All dimensions are for reference only.

UCACSR can also cut:

- ACSR wire 954 kcmil (Cardinal)
- 5/8" (20 mm) Standard Guy Strand
- 1/2" (13 mm) EHS Guy Strand
- 1/2" (13 mm) Ground Rod
- 1/2" (13 mm) Rebar (schedule 60)

							UC** and UCASCR CABLE CUTTER BLADES
							CUSTOMER DRAWING
							O0084SLU_DC/00
							UNLESS OTHERWISE SPECIFIED, MATERIAL: DIMENSIONAL TOLERANCES ARE:
							(.x) ± (.xxx) ± (.xxx) ±
00	7-29-16	BKA	ACC	JADE	DRAWING RELEASED	010062	THIRD ANGLE PROJECTION DRAWING NUMBER: 00084SLU_DC
REV	DATE	BY	СНК	APR	DESCRIPTION	ECN	BKA DATE: CHK SCALE NONE SHT 1 OF 1 B SIZE B B