
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT * PART NO.	BUNDLE MIN. (mm)	1	A in (mm)	D c (mm	C in (mm)	(mm)	Lice (REF)	L cmm (REF)		T cm) in (mm)	(mm)	in (REF)	M in (mm)	N (mm)		MIN. LOOP TENSILE Ibs. (N)	CROSS SECTION	WEIGHT bs./100 pcs.
PRA2S-A	.25 (6.4)	1.85 (47.0)	.052 (1.3)	.190 (4.8)	.258 (6.6)	.220 (5.6)	.316 (8.0)	8.5 (216)	.148 (3.8)	.90 (22.9)	1.00 (25.4)	.200 (5.1)	.134 (3.4)	7.3 (185)	300 (7.6)	.600 (15.2)	50 (222)	STANDARD	.53 (242)

NOTES:

- 1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATIONS FOR PACKAGE SIZE. TO APPLY MOUNTS:
 - 1) REMOVE PROTECTIVE LINER FROM MOUNT.

 - 2) PLACE IN DESIRED LOCATION. 3) APPLY PRESSURE TO TOP SURFACE OF MOUNT.

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENWEZLAYERS G00239EV_PB_PRA2S_01

JU CORP.

TINLEY PARK, ILLINOIS

COMBINATION ADHESIVE MOUNT/TIE PRA SERIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (,X) ±0.05(1.31(.XXX) ±0.010(0.25)
(YY) AO OO LO EL ANGLES A SI

ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD MILE PROJECTION.

UNLESS OTHERWISE SPECIFIED.

CGSM	MAT'LE
------	--------

NONE

<u> </u>														
	1	4/28/04	Ş		UPDATE DRAWING, ADD REF TO SEVERAL DIMENSIONS	680239EV 1 ECN - R CUST					DATE 1/22/97	NYLON 6/6	GB0239EV	D=0 A
	REV	DATE	BY	снк	DESCRIPTION			CUST	SUP		CHK'D			SIZE