

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




Ø 0.490

[12.446]

[7.874]



PANDUIT	WEIGHT					
PART	bs/100 pcs					
NUMBER*	(g)/100 pcs					
TMSH50	2.06 (937)					



NOTES:

*1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

DIMENSIONS	ΙN	BRACKETS	ARE	METRIC	[mm]
------------	----	----------	-----	--------	---	----	---

CAD FILENAME/LAYERS

G00239CQ_PB_TMSH50_A_04.PRT

											YDUIT corp.	TINLEY PARK, ILLINO	IS
4	6-27/01	LGG		UPDATED AND ADDED REF	GB0239C0	4				-	TMSH50 FRAME MOUNTED		
3	07/26/00	GDL		1) DIM .310 MIN WAS .310. 2) MATERIAL WAS POLYPROPYLENE, GLASS FILLED 3) WEIGHT WAS 2.03/(924)	GB0239C0	3					SHOULDERED ST	ANDOFF	
3	07726700	GDH			G00239C0						THERWISE SPECIFIED, NAL TOLERANCES ARE:	UNLESS OTHERWISE SPECIFIED.	
2	04/18/96	GDH		REVISED TO REFLECT NEW PART GEOMETRY	GB0239C0	2				(.X) ±0.05(1.3)(.XXX)±0.010(0.25) (.XX)±0.02(0.5)ANGLES±5*		ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
1	07/25/95	GDH		REVISED PART GEOMETRY AND WEIGHT	GB0239C0	1				DRAWN BY GDH	MAT'L: HEAT STABILIZED	SCALE FULL	
R	03/28/95	GDH		INITIAL RELEASE	GB0239C0	R				07/25/95	I WEATHER REGISTANT	DRAWING NO.	DWG
REV	DATE	ВҮ	СНК	DESCRIPTION	ECN - R CU		CUST SU			CHK *D	COLOR BLACK	GB0239CQ	SIZE
L	l		I		1		1	I	l .		1	ı	Ь_