




1		2		3		4		5		6		7		8																																																																																																	
				REV.	ECN NO.	DATE		SIGN		DESCRIPTION																																																																																																					
				B	C180431	2018-11-27		Allen Pan		統一料號與圖檔檔名，增加共用PIN視圖																																																																																																					
				C	C180533	2018-12-19		Allen Pan		增加AWG數說明及變更線長標註																																																																																																					
				D	C190057	2019-01-10		Allen Pan		變更芯線顏色，取消芯線印字																																																																																																					
QC L (Order Information)																																																																																																															
<table><tr><td>4</td><td>--</td><td>4</td><td>--</td><td>4</td><td>Orange</td><td>橘</td></tr><tr><td>3</td><td>Red</td><td>3</td><td>Red</td><td>3</td><td>Red</td><td>紅</td></tr><tr><td>2</td><td>Brown</td><td>2</td><td>Brown</td><td>2</td><td>Brown</td><td>棕</td></tr><tr><td>1</td><td>--</td><td>1</td><td>Black</td><td>1</td><td>Black</td><td>黑</td></tr><tr><td>PE</td><td>Yellow</td><td>PE</td><td>Yellow</td><td>PE</td><td>Yellow</td><td>黃</td></tr><tr><td>Pin #</td><td>Wire</td><td>Pin #</td><td>Wire</td><td>Pin #</td><td>Wire</td><td></td></tr><tr><td colspan="7"></td></tr><tr><td colspan="7"></td></tr><tr><td colspan="7"></td></tr><tr><td colspan="7">Pin Assignments Front View</td></tr></table>																4	--	4	--	4	Orange	橘	3	Red	3	Red	3	Red	紅	2	Brown	2	Brown	2	Brown	棕	1	--	1	Black	1	Black	黑	PE	Yellow	PE	Yellow	PE	Yellow	黃	Pin #	Wire	Pin #	Wire	Pin #	Wire																							Pin Assignments Front View																																
4	--	4	--	4	Orange	橘																																																																																																									
3	Red	3	Red	3	Red	紅																																																																																																									
2	Brown	2	Brown	2	Brown	棕																																																																																																									
1	--	1	Black	1	Black	黑																																																																																																									
PE	Yellow	PE	Yellow	PE	Yellow	黃																																																																																																									
Pin #	Wire	Pin #	Wire	Pin #	Wire																																																																																																										
Pin Assignments Front View																																																																																																															
Notes: * Waterproof Rate: IP68(1M, 24Hour). * Connector: Nylon+GF, Black. * Pin Contact: Brass, Ni&Au Plated. * Screw Nut: Zinc Alloy, Nickel Plated. * Outer Mold: PP, Black. * Cable: (S) AC 630V, 14 AWG, PUR Jacket. (G) AC 630V, 14 AWG, PVC Jacket. * Rated Voltage: 630V AC. * Rated Current: 12A * Operating Temperature: -25~85°C * Cable Length Tolerance: 01M:±40mm 02M~05M:±60mm 06M~10M:±100mm 11M~30M:±200mm 31M~99M:±500mm ALTW CONFIDENTIAL 2019-01-10 R&D DEPT.																																																																																																															
<table><tr><td colspan="2">UNIT:mm</td><td colspan="2"></td><td colspan="4">TITLE</td><td colspan="2">ITEM NO</td><td colspan="2">DRAWN BY</td><td colspan="2">DATE</td></tr><tr><td colspan="2">TOLERANCE</td><td colspan="2"></td><td colspan="4">M12 K-CODE, STRAIGHT, FEMALE CONN + CABLE</td><td colspan="2">DWG NO</td><td colspan="2">CHECKED BY</td><td colspan="2">DATE</td></tr><tr><td colspan="2">±0.5mm</td><td colspan="2"></td><td colspan="2">SCALE</td><td colspan="2">SIZE</td><td colspan="2">SHEET</td><td colspan="2">OF</td><td colspan="2"></td></tr><tr><td colspan="2"></td><td colspan="2"></td><td colspan="2">1.200</td><td colspan="2">A4</td><td colspan="2">1</td><td colspan="2">2</td><td colspan="2"></td></tr><tr><td colspan="2"></td><td colspan="2"></td><td colspan="2">REV.</td><td colspan="2">WC-REV.</td><td colspan="2">QC</td><td colspan="2">Inspection item</td><td colspan="2"></td></tr><tr><td colspan="2"></td><td colspan="2"></td><td colspan="2">D</td><td colspan="2">A.19</td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td></tr></table> Amphenol LTW 安費諾亮泰企業股份有限公司 <table><tr><td colspan="2">CUSTOMER</td><td colspan="2">APPROVED BY</td><td colspan="2">DATE</td></tr><tr><td colspan="2">ALTW</td><td colspan="2">Fred Lee</td><td colspan="2">2019-01-10</td></tr></table>																UNIT:mm				TITLE				ITEM NO		DRAWN BY		DATE		TOLERANCE				M12 K-CODE, STRAIGHT, FEMALE CONN + CABLE				DWG NO		CHECKED BY		DATE		±0.5mm				SCALE		SIZE		SHEET		OF								1.200		A4		1		2								REV.		WC-REV.		QC		Inspection item								D		A.19								CUSTOMER		APPROVED BY		DATE		ALTW		Fred Lee		2019-01-10	
UNIT:mm				TITLE				ITEM NO		DRAWN BY		DATE																																																																																																			
TOLERANCE				M12 K-CODE, STRAIGHT, FEMALE CONN + CABLE				DWG NO		CHECKED BY		DATE																																																																																																			
±0.5mm				SCALE		SIZE		SHEET		OF																																																																																																					
				1.200		A4		1		2																																																																																																					
				REV.		WC-REV.		QC		Inspection item																																																																																																					
				D		A.19																																																																																																									
CUSTOMER		APPROVED BY		DATE																																																																																																											
ALTW		Fred Lee		2019-01-10																																																																																																											
W10814-03-0001A2																																																																																																															

Order Information:



UNIT:mm



TOLERANCE

 $\pm 0.5\text{mm}$ TITLE
M12 K-CODE, STRAIGHT, FEMALE CONN
+ CABLE

SCALE 1.000	SIZE A4	SHEET 2	OF 2
REV. D	WC-REV. A.19	QC: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Allen Pan	DATE 2019-01-10
DWG NO M12K-XXBFFM-SL8XXX	CHECKED BY Fred Lee	DATE 2019-01-10
CUSTOMER ALTW	APPROVED BY Fred Lee	DATE 2019-01-10