



TOLERANCE DETAILS					
1	D	+ 0.000 [ + 0.00] - 0.015 [-0.38]	6	SD	± 0.005 [± 0.13]
2	L	± 0.015 [± 0.38]	7	SL	± 0.010 [± 0.25]
3	W	+ 0.000 [ + 0.00] - 0.010 [-0.25]	8	TL	± 0.010 [± 0.25]
4	HD	± 0.005 [± 0.13]	9	WL	+ 0.000 [ + 0.00] - 0.010 [-0.25]
5	HL	+ 0.000 [ + 0.00] - 0.015 [-0.38]			



1. Material : Stainless Steel
2. Finish : No Plating
3. ASME Y14.5-M - 2009
4. All Drawing Dimensions are in Inches [mm]
5. Unless otherwise specified; Edge Breaks, Radii or Countersinks 0.005-0.015



This Drawing is the Property of RAF.  
It contains confidential, proprietary  
information that is RAF property. Do  
not disclose to or duplicate for others  
except as authorized by RAF.

**TOLERANCES**  
ALL DIMENSIONS ARE INCHES  
(UNLESS OTHERWISE SPECIFIED)

**METALLIC**  
LENGTHS  $\leq 6$  INCHES  $\pm 0.005$   
LENGTH  $> 6$  INCHES  $\pm 0.010$   
DIAMETERS:  $\pm 0.005$

**NON-METALLIC**  
LENGTH:  $\pm 0.010$  DIAMETERS:  $\pm 0.010$

**INTERNAL THREADS:**  
MINIMUM THREAD DEPTH

COMPONENT	PANEL SCREW
<p>0824-SS</p> <p>CAPTIVE PANEL SCREW STYLE 4</p>	SCALE
	7.56
	SHEET
	1 of 1