

6		5		4		3		2		1	
ITEM	PART#	DESCRIPTION			QTY	UOM		FROM	TO	DESCRIPTION	COLOR
A	430200200	MicroFit 3.0 Plug DR PnlMnt 2Ckt			1	PC		A1	--	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
B	430310023	MICROFIT 3.0 M CRP TERM CHN 30AU 18AWG			2	PC		A2	--	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
C	--	PAPER PRINTED PAPER WHITE			1	PC					




TABLE			
PART NUMBER	L1	L2	TITLE
2147582021	150±8	63REF	MICRO-FIT3.0 P-S 2 CIRCUIT 150MM Au
2147582022	300±10	138REF	MICRO-FIT3.0 P-S 2 CIRCUIT 300MM Au
2147582023	600±10	287REF	MICRO-FIT3.0 P-S 2 CIRCUIT 600MM Au

- NOTES
- Connector view shown is from mating side.
 - Free ends must be stripped, twisted & tinned. The length of tinning is 5±1mm. Tinning dia must be 1.39mm Max.
 - Label text must be 2mm max. in height with Arial font.
 - Label must be wrapped in Flag type.

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

REVISION			
DATE	REV	DESCRIPTION	CHANGER
30/12/2019	A	INITIAL RELEASE	ARAJU

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex SEE TABLE			
 = 0		mm		NTS								
 = 0		GENERAL TOLERANCES (UNLESS SPECIFIED)										
 = 0		ANGULAR TOL ± °				EC NO: 629791 DRWN: ARAJU						

DOCUMENT STATUS	P1	RELEASE DATE	2020/01/18	09:07:16
-----------------	----	--------------	------------	----------